



Heng Balance Lamp is the RedDot award-winning design of 2016. The lamp is controlled in a unique way: by pulling the lower sphere toward the one that is hanging from the top. The magnetic tension force will keep suspended in mid-air and the lighting element embedded in the frame will turn on.

## **Contains:**

Magnet: 2\* 10x10 mm, N35

LED Strip: 5V, 3-4W, Width:6mm / LED Diffuser Panel / USB Cable



## **Instructions:**

- 1. Magnetic Switch: Pull up the lower sphere. The lamp will light up when the 2 spheres meet in mid-air.
- 2. Compatibility: The USB cable is compatible with all other adaptors, which can transfer 100-240 V to 5 V.
- 3. LED Light: The LED last for more than 50,000 hrs.

## **Product Care:**

- 1. The Heng Balance Lamp is USB powered. It only needs to be plugged into an adaptor with a maximum output of 5V to power it.
- 2. Pull up the lower sphere gently when switching on the lamp.
- 3. Place down the lower sphere gently to the top of the base when switch off the lamp, the embedded magnet beneath the surface will properly secure the sphere in place.
- 4. Avoid high humid and high temperature area
- 5. For defective claims or replacement within the 2 years manufacturer warranty, please contact DesignNest customer service team for further assistance. Check DesignNest global limited warranty for more details.

Contact:

DesignNest Inc.
Attn: Customer service
1901 E Carnegie Ave Suite 1B Santa Ana CA 92705
Phone: 714-617-4883 Email: support.us@designnest.com
www.designnest.com